



TRB302B



Module 2 inputs flush mounted 230V KNX QL

Technical Features

Architecture

Bus system	Radio frequent
------------	----------------

Settings

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

Electric current

Number of entry circuits	2
--------------------------	---

Equipment

External signal voltage necessary	No
-----------------------------------	----

Connectivity

With bus system KNX radio	Yes
---------------------------	-----

Equipment

Radio frequency bidirectional	No
With battery	No
With HVAC control	No

Frequency

Frequency transmission	868 - 868 MHz
------------------------	---------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Lighting

LED controlling	No
-----------------	----

Materials

Material	Plastic
Colour	Light grey
RAL code	7035

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Cable

Cable length	0.20 m
--------------	--------

Voltage

Input voltage	5 - 5 V
Type voltage supply	AC

Texts

Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals

Sustainability

RoHS conform	Yes
--------------	-----