



TRB302B



Module 2 inputs flush mounted 230V KNX QL

Technical Features

Architecture

Bus system Radio frequent

Settings

Supported configuration mode ETS
easy
quicklink

Electric current

Number of entry circuits 2

Equipment

External signal voltage necessary No

Connectivity

With bus system KNX radio Yes

Equipment

Radio frequency bidirectional No

With battery No

With HVAC control No

Frequency

Frequency transmission 868 - 868 MHz

Installation, mounting

Mounting on Flush mounting

Lighting

LED controlling No

Materials

Material Plastic

Colour Light grey

RAL code 7035

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature -5 - 45 °C

Cable

Cable length 0.20 m

Voltage

Input voltage 5 - 5 V

Type voltage supply AC

Texts

Installation mode For installation behind flush-mounted inserts

Type of connection With screw-in lift terminals

Sustainability

RoHS conform Yes