



TRB302B



**Module 2 inputs flush mounted 230V KNX QL**

**Technical Features**

**Architecture**

Bus system	Radio frequent
------------	----------------

**Settings**

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

**Electric current**

Number of entry circuits	2
--------------------------	---

**Equipment**

External signal voltage necessary	No
-----------------------------------	----

**Connectivity**

With bus system KNX radio	Yes
---------------------------	-----

**Equipment**

Radio frequency bidirectional	No
-------------------------------	----

With battery	No
--------------	----

With HVAC control	No
-------------------	----

**Frequency**

Frequency transmission	868 - 868 MHz
------------------------	---------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Lighting**

LED controlling	No
-----------------	----

**Materials**

Material	Plastic
----------	---------

Colour	Light grey
--------	------------

RAL code	7035
----------	------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Cable**

Cable length	0.20 m
--------------	--------

**Voltage**

Input voltage	5 - 5 V
---------------	---------

Type voltage supply	AC
---------------------	----

**Texts**

Installation mode	For installation behind flush-mounted inserts
-------------------	---

Type of connection	With screw-in lift terminals
--------------------	------------------------------

**Sustainability**

RoHS conform	Yes
--------------	-----