



41491404

SCHUKO sock. outl. w. lab. field a. enh. cont. prot., Q.x, alu velvety, lacq.

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Aluminium

RAL code 9006

Surface finish Velvety

Material Duroplastic

Treatment Varnished

Dimensions

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth flush-mounted boxes 31 mm

Built-in depth 32 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field Yes

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes

Impact resistance IK IK02

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Central cover plate

Protection Enhanced contact protection

Texts

Type of connection	With screw-in lift terminals
Labelling	With labelling field

Suitable for

Q.x

Sustainability

RoHS conform	Yes
--------------	-----