




WGCXR122NB

16AX 2G 2W round switch;nb

Technical Features

Electric current

Switching current	16 A
-------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Bronze
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

Controls and indicators

Number of buttons	2
-------------------	---

Dimensions

Dimensions	86 x 86 mm
Built-in depth flush-mounted boxes	35 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Double push button
---------------------------	--------------------

Electric current

Rated current	16 A
---------------	------

Texts

Switch mode	2-way
-------------	-------

Sustainability

RoHS conform	Yes
--------------	-----