



VD104NF

Small distributor, IC², surface, 1row, 4M, IP30, MS-terminal, N, without door

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	4
-------------------	---

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	163.50 mm
Width	81.50 mm
Depth	71 mm

Cover, door

Number of cabinet doors	0
Number of locks	0

Dimensions

Number of width units	4
-----------------------	---

Materials

Material	Polystyrene (PS)
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	No
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	650 °C

Sustainability

Halogen free	Yes
RoHS conform	Yes