



VD104NT

Sm.distr.,VD/IC<sup>2</sup>,surface,1row,4M,IP30,no terminals,AUS,without door

**Technical Features**

**Voltage**

Nominal voltage 400 - 400 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Surface mounting

**Electric current**

Rated current 63 A

**Equipment**

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block No

**Capacity**

Number of modules 4

**Functions**

With conduit inlets Yes

**Dimensions**

Height 163.50 mm

Width 81.50 mm

Depth 71 mm

**Cover, door**

Number of cabinet doors 0

Number of locks 0

**Dimensions**

Number of width units 4

**Materials**

Material Plastic

RAL code 9010

Colour Pure white

**Equipment**

Has earthing terminal block No

Has mounting plate No

**Materials**

Ultraviolet-resistant No

**Safety**

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP30

Locking type Without lock

Glow wire test 750 °C

**Sustainability**

Halogen free Yes

RoHS conform Yes