



50753515



Push-button, 2 change-over contacts surf.-mtd, isolated input term., W.1, grey matt

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Materials

Colour Grey

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Transparent No

Dimensions

Height 55.90 mm

Width 55.90 mm

Depth 32.30 mm

Built-in depth flush-mounted boxes 0 mm

Installation, mounting

Mounting on Surface mounting

Controls and indicators

Type of push button Series push button

Safety

Ingress Protection (IP) class IP55

Impact resistance IK IK05

Accessories

Has labelling field No

Use conditions

Operating temperature -25 - 35 °C

Texts

Imprint Without imprint

Installation mode For screw fastening

Sealing With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Terminal With Wago clip-in 2-wire connection terminal for wiring
With two clip-in places for Wago 2-wire connection terminals in the housing floor

Type of connection With plug-in terminals