

# Product Datasheet

## VF212PF



VF212PF3

Small distributor,golf,flush,2row,24M,IP40,MS-terminal,PE,white door

### Technical Features

#### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

#### Installation, mounting

|                            |                |
|----------------------------|----------------|
| Suitable for outdoor usage | No             |
| Mounting on                | Flush mounting |

#### Electric current

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

#### Equipment

|                            |    |
|----------------------------|----|
| Number of rails            | 2  |
| Number of rows             | 2  |
| Number of section in width | 1  |
| With lock                  | No |
| Has neutral terminal block | No |

#### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 24 |
|-------------------|----|

#### Functions

|                            |     |
|----------------------------|-----|
| Has protection main switch | No  |
| With conduit inlets        | Yes |

#### Scope of delivery

|                             |   |
|-----------------------------|---|
| Number of RCCB in enclosure | 0 |
|-----------------------------|---|

#### Dimensions

|                 |          |
|-----------------|----------|
| Height          | 418 mm   |
| Width           | 382 mm   |
| Depth           | 97.50 mm |
| Built-in height | 382 mm   |
| Built-in width  | 318 mm   |

#### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

#### Dimensions

|                |       |
|----------------|-------|
| Built-in depth | 72 mm |
|----------------|-------|

#### Cover, door

|                 |   |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

#### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 12 |
|-----------------------|----|

#### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

#### Materials

|          |            |
|----------|------------|
| Material | Plastic    |
| RAL code | 9010       |
| Colour   | Pure white |

#### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

#### Materials

|                       |    |
|-----------------------|----|
| Ultraviolet-resistant | No |
|-----------------------|----|

Product Datasheet

VF212PF

|                               |                              |
|-------------------------------|------------------------------|
| Safety                        |                              |
| Protection class              | Isolation class II           |
| Impact resistance IK          | IK07                         |
| Ingress Protection (IP) class | IP40                         |
| Locking type                  | Snap on lock<br>Without lock |
| Glow wire test                | 650 °C                       |
| Sustainability                |                              |
| RoHS conform                  | Yes                          |