



WMSU83R

13A FCU Unswitched with Red Face Plate

Technical Features

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Red

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Dimensions

Dimensions 86 x 86 mm

Safety

Ingress Protection (IP) class IP20

Electric current

Rated current 13 A

Texts

Installation mode Front mounting

Type of connection With screw terminals

Sustainability

REACH-SVHC free Yes

RoHS conform Yes