



FD62GN

Enclosure, NewVegaD, 1050x550x193mm, 144 modules, surface-mounted, empty

Technical Features

Dimensions

| | |
|-----------------------|---------|
| Height | 1050 mm |
| Width | 550 mm |
| Depth | 193 mm |
| Thickness of sidewall | 1 mm |

Safety

| | |
|-------------------------------|--------------------|
| Ingress Protection (IP) class | IP30 |
| Protection class | Isolation class II |
| Locking type | Without lock |
| Impact resistance IK | IK07 |

Equipment

| | |
|---------------------------------|---|
| Number of flange plate openings | 2 |
|---------------------------------|---|

Installation, mounting

| | |
|----------------------------|------------------|
| Mounting on | Surface mounting |
| Suitable for outdoor usage | No |

Materials

| | |
|-----------|------------------|
| Colour | Pure white |
| RAL code | 9010 |
| Treatment | Powder coated |
| Material | Metal Plastic |

Equipment

| | |
|----------------|---|
| Number of rows | 6 |
|----------------|---|

Cover, door

| | |
|---------------------------|----|
| Number of cabinet doors | 0 |
| Door/cover is transparent | No |

Electric current

| | |
|---------------|-------|
| Rated current | 160 A |
|---------------|-------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|