



VD103NT

Sm.distr.,VD/IC²,surface,1row,3M,IP30,no terminals,AUS,without door

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 63 A

Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block No

Capacity

Number of modules 3

Functions

With conduit inlets Yes

Dimensions

Height 163.50 mm

Width 63.50 mm

Depth 71 mm

Cover, door

Number of cabinet doors 0

Number of locks 0

Dimensions

Number of width units 3

Materials

Material Plastic

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block No

Has mounting plate No

Materials

Ultraviolet-resistant No

Safety

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP30

Locking type Without lock

Glow wire test 750 °C

Sustainability

Halogen free Yes

RoHS conform Yes