



VD103NT

Sm.distr.,VD/IC²,surface,1row,3M,IP30,no terminals,AUS,without door

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	3
-------------------	---

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	163.50 mm
Width	63.50 mm
Depth	71 mm

Cover, door

Number of cabinet doors	0
Number of locks	0

Dimensions

Number of width units	3
-----------------------	---

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	No
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	750 °C

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes