

Product Datasheet

29517006



29517006



LED signal light, RGB, K.1, ant. matt, lacq.

Technical Features

Voltage

Rated voltage	230 V
---------------	-------

Power

Power absorbed	2 W
----------------	-----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Lighting

Type of lamp	LED
--------------	-----

Materials

Colour	Anthracite
RAL code	7021
Surface finish	Matt
Material	Metal Plastic
Treatment	Varnished

Dimensions

Height	70 mm
Width	70 mm
Depth	50 mm

Connection

Conductor cross-section	2.50 - 2.50 mm ²
-------------------------	-----------------------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Lighting	Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button Colour sequence can be stopped at any position via the push-button.
Labelling	Foils with imprint of symbols insertable
Imprint	Without imprint