



29517004



LED signal light, RGB, Q.1/Q.3, stainless steel matt, lacq.

**Technical Features**

**Voltage**

Rated voltage 230 V

**Power**

Power absorbed 2 W

**Frequency**

Frequency 50 - 60 Hz

**Lighting**

Type of lamp LED

**Materials**

Colour Stainless steel

RAL code 9022

Surface finish Matt

Material Metal  
Plastic  
Stainless steel

Treatment Varnished

**Dimensions**

Height 70 mm

Width 70 mm

Depth 50 mm

**Connection**

Conductor cross-section 2.50 - 2.50 mm<sup>2</sup>

**Safety**

Ingress Protection (IP) class IP20

**Texts**

Lighting Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button  
Colour sequence can be stopped at any position via the push-button.

Labelling Foils with imprint of symbols insertable

Imprint Without imprint