

# Product Datasheet

## 85342273



85342273



### IR motion detector comfort 2.2 m, K.5, stainless steel matt, lacquered

#### Technical Features

##### Dimensions

Installation height	2.20 - 2.20 m
Assembling height	34 mm

##### Detection

Type of sensor	Movement detector
Detection diameter on floor	0 - 0 m
Detection angle adjustable	45 - 90 °

##### Materials

Colour	Stainless steel
Surface finish	Matt
Treatment	Varnished
Material	Stainless steel Thermoplastic

##### Reach distance

Max. transmission range frontally	8 m
Max. transmission range sideways	6 m

##### Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

##### Settings

Response brightness adjustable	Yes
--------------------------------	-----

##### Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Texts

Function	With memory function for presence simulation Teach function for response brightness via button With keylock Party function for switching on for 2 hours
Protection	With dismantling protection

##### Sustainability

RoHS conform	Yes
--------------	-----