



FU72DN

Enclosure, NewVegaD, 1287x550x150mm, 168 modules, flush-mounted, distribution

Technical Features

Installation, mounting

| | |
|----------------------------|----------------|
| Suitable for outdoor usage | No |
| Mounting on | Flush mounting |

Electric current

| | |
|---------------|-------|
| Rated current | 160 A |
|---------------|-------|

Equipment

| | |
|----------------------------|----|
| Number of rails | 7 |
| Number of rows | 7 |
| Number of section in width | 2 |
| With lock | No |
| Has neutral terminal block | No |

Capacity

| | |
|-------------------|-----|
| Number of modules | 168 |
|-------------------|-----|

Dimensions

| | |
|-----------------------|---------|
| Height | 1287 mm |
| Width | 600 mm |
| Depth | 150 mm |
| Built-in width | 550 mm |
| Built-in depth | 110 mm |
| Number of width units | 24 |

Cover, door

| | |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

Connection

| | |
|--------------------------|---|
| Number of conduit inlets | 4 |
|--------------------------|---|

Materials

| | |
|----------|------------------|
| Material | Metal Plastic |
| RAL code | 9010 |
| Colour | Pure white |

Equipment

| | |
|-----------------------------|----|
| Has earthing terminal block | No |
| Has mounting plate | No |

Safety

| | |
|-------------------------------|--------------------|
| Protection class | Isolation class II |
| Impact resistance IK | IK07 |
| Ingress Protection (IP) class | IP30 |
| Locking type | Without lock |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|