

Product Datasheet

85342289



85342289



IR motion detector comfort 2.2 m, S.1/B.3/B.7, polar white, glossy

Technical Features

Dimensions

Installation height	2.20 - 2.20 m
Assembling height	34 mm

Detection

Type of sensor	Movement detector
Detection diameter on floor	0 - 0 m
Detection angle adjustable	45 - 90 °

Materials

Colour	Polar white
Surface finish	Glossy
Treatment	Untreated
Material	Thermoplastic

Reach distance

Max. transmission range frontally	8 m
Max. transmission range sideways	6 m

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Settings

Response brightness adjustable	Yes
--------------------------------	-----

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Function	With memory function for presence simulation Teach function for response brightness via button With keylock Party function for switching on for 2 hours
Protection	With dismantling protection

Sustainability

RoHS conform	Yes
--------------	-----