



845712503

**Integro Insert- Power Socket Outlet 12V Black Matt**

**Technical Features**

**Voltage**

Rated voltage	12 V
---------------	------

**Electric current**

Rated current	20 A
---------------	------

**Voltage**

Output voltage	12-24 V
----------------	---------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Power**

Output power	240 W
--------------	-------

**Materials**

Colour	Black
RAL code	9005 9011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	55.50 mm
Width	55.50 mm
Built-in depth flush-mounted boxes	46 mm

**Connection**

Connector/plug type	Ring lug
---------------------	----------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting

**Equipment**

Rotated central insert	No
With hinged lid	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	1
-------------------	---

**Safety**

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

---

**Texts**

Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With flat connection

---

**Suitable for**

integro

---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes