

# Product Datasheet

## 845712509



845712509

### Integro Insert-Power Socket Outlet 12V Polar White Glossy

#### Technical Features

##### Electric current

Rated current	20 A
---------------	------

##### Voltage

Rated voltage	12 V
Nominal voltage	12-24 V
Output voltage	12-24 V

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Power

Output power	240 W
--------------	-------

##### Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

##### Dimensions

Height	55.50 mm
Width	55.50 mm
Built-in depth flush-mounted boxes	46 mm

##### Connection

Connector/plug type	Ring lug
---------------------	----------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

##### Equipment

Rotated central insert	No
With hinged lid	No
With signal lamp	No
With lock	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	1
-------------------	---

##### Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Central cover plate

<b>Texts</b>	
Protection	Without enhanced contact protection
Type of connection	With flat connection

<b>Suitable for</b>	
integro	

<b>Sustainability</b>	
Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes