



85342239



**IR motion detector comfort 2.2 m, R.1/R.3/1930/R.classic, polar white glossy**

**Technical Features**

**Dimensions**

|                     |               |
|---------------------|---------------|
| Installation height | 2.20 - 2.20 m |
| Assembling height   | 34 mm         |

**Detection**

|                             |                   |
|-----------------------------|-------------------|
| Type of sensor              | Movement detector |
| Detection diameter on floor | 0 - 0 m           |
| Detection angle adjustable  | 45 - 90 °         |

**Materials**

|                |               |
|----------------|---------------|
| Colour         | Polar white   |
| Surface finish | Glossy        |
| Treatment      | Untreated     |
| Material       | Thermoplastic |

**Reach distance**

|                                   |     |
|-----------------------------------|-----|
| Max. transmission range frontally | 8 m |
| Max. transmission range sideways  | 6 m |

**Lighting**

|                                |             |
|--------------------------------|-------------|
| Response brightness adjustable | 5 - 1000 lx |
|--------------------------------|-------------|

**Settings**

|                                |     |
|--------------------------------|-----|
| Response brightness adjustable | Yes |
|--------------------------------|-----|

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Texts**

|            |  |
|------------|--|
| Function   | With memory function for presence simulation<br>Teach function for response brightness via button<br>With keylock<br>Party function for switching on for 2 hours |
| Protection | With dismantling protection  |

**Connectivity**

|             |     |
|-------------|-----|
| Connectable | Yes |
|-------------|-----|

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|