

Product Datasheet

845712507



845712507

Integro Insert-Power Socket Outlet 12V Grey Glossy

Technical Features

Electric current

Rated current	20 A
---------------	------

Voltage

Rated voltage	12 V
Nominal voltage	24 - 24 V
Output voltage	12-24 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Output power	240 W
--------------	-------

Materials

Colour	Grey
RAL code	7038
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	55.50 mm
Width	55.50 mm
Built-in depth flush-mounted boxes	46 mm

Connection

Connector/plug type	Ring lug
---------------------	----------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Rotated central insert	No
With hinged lid	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Central cover plate

Product Datasheet

845712507

Texts	
Protection	Without enhanced contact protection
Type of connection	With flat connection

Suitable for	
integro	

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes