



85342139



**Motion det. 2.2 m, R.1/R.3/1930/R.cl., p. white glossy**

**Technical Features**

**Dimensions**

Installation height	2.20 - 2.20 m
Assembling height	34 mm

**Detection**

Type of sensor	Movement detector
Detection diameter on floor	0 - 0 m
Detection angle adjustable	45 - 90 °

**Materials**

Colour	Polar white
Surface finish	Glossy
Treatment	Untreated
Material	Thermoplastic

**Reach distance**

Max. transmission range frontally	8 m
Max. transmission range sideways	6 m

**Lighting**

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

**Settings**

Response brightness adjustable	Yes
--------------------------------	-----

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Texts**

Function	With memory function for presence simulation Teach function for response brightness via button With keylock Party function for switching on for 2 hours
Protection	With dismantling protection

**Connectivity**

Connectable	Yes
-------------	-----

**Sustainability**

RoHS conform	Yes
--------------	-----