

# Product Datasheet

## ATA122009016



ATA122009016

### Trunking 12x20,L=2,1m,traffic white

#### Technical Features

##### Dimensions

Height	13 mm
Width	24 mm
Length	2100 mm
Inner cross-section	240 - 240 mm <sup>2</sup>

##### Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	1
--	---

##### Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9016
Colour	Traffic white

##### Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

##### Standards

Suitable for functional integrity according to DIN4102-12	No
---	----

##### Use conditions

Operating temperature	15 - 60 °C
-----------------------	------------

##### Connectivity

Trunking coupling	Without coupling
-------------------	------------------

##### Equipment

Number of partitions	0
Number of compartments	1 - 1
Number of pluggable partitions	0
Cable retaining clip included	Yes
With protective film	No

##### Installation, mounting

Base perforation	No
------------------	----

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

**Illustrations | Drawings**

