



85342173



Motion det. 2.2 m, K.5, stainless steel matt, lacq.

Technical Features

Dimensions

| | |
|---------------------|---------------|
| Installation height | 2.20 - 2.20 m |
| Assembling height | 34 mm |

Detection

| | |
|-----------------------------|-------------------|
| Type of sensor | Movement detector |
| Detection diameter on floor | 0 - 0 m |
| Detection angle adjustable | 45 - 90 ° |

Materials

| | |
|----------------|----------------------------------|
| Colour | Stainless steel |
| Surface finish | Matt |
| Treatment | Varnished |
| Material | Stainless steel Thermoplastic |

Reach distance

| | |
|-----------------------------------|-----|
| Max. transmission range frontally | 8 m |
| Max. transmission range sideways | 6 m |

Lighting

| | |
|--------------------------------|-------------|
| Response brightness adjustable | 5 - 1000 lx |
|--------------------------------|-------------|

Settings

| | |
|--------------------------------|-----|
| Response brightness adjustable | Yes |
|--------------------------------|-----|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|------------|--|
| Function | With memory function for presence simulation Teach function for response brightness via button With keylock Party function for switching on for 2 hours |
| Protection | With dismantling protection |

Connectivity

| | |
|-------------|-----|
| Connectable | Yes |
|-------------|-----|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|