



16326089

Centre plate for mechanical timer, Q.1/Q.3, p. white velvety

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Velvety
Material	Duroplastic
Treatment	Untreated

Dimensions

Height	58 mm
Width	58 mm
Depth	24 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Monitoring window/light outlet	No
--------------------------------	----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Imprint	With time scale symbol imprint
Installation mode	For screw fastening

Identification

Assembly arrangement	Central cover plate
----------------------	---------------------

Suitable for

Q.x	
-----	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes