



16517309

Rocker f. accessible const., tactile symbol f. door, redlens , K.1, p.white gl.

Technical Features

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Materials

| | |
|----------------|---------------|
| Colour | Polar white |
| RAL code | 9010 |
| Surface finish | Glossy |
| Material | Thermoplastic |
| Treatment | Untreated |

Dimensions

| | |
|--------|----------|
| Height | 54.90 mm |
| Width | 55.70 mm |
| Depth | 22 mm |

Connectivity

| | |
|---------------|----------------|
| Mounting type | Clamp mounting |
|---------------|----------------|

Equipment

| | |
|--------------------------------|-----|
| Monitoring window/light outlet | Yes |
|--------------------------------|-----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP44 |
| Impact resistance IK | IK05 |

Texts

| | |
|----------------------------------|--|
| Imprint | Without imprint |
| Installation mode | Clamp fastening |
| Push button | Also for KNX applications: push-button, 1-gang |
| Rocker switch/rocker push-button | For illuminated rocker push-buttons |

Suitable for

| | |
|-----|--|
| K.x | |
|-----|--|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |