



EH711



IP20



**Daily time switch 1 channel, analog, 72x72 with power reserve**

**Technical Features**

**Equipment**

Number of channels 1

**Frequency**

Frequency 50 - 60 Hz

**Power**

Power consumption during operation 0.50 VA

230 V incandescent and halogen lamp 1000 W

Power incandescent lamp 1000 - 1000 W

**Functions**

Number of function channels 1

**Connection**

Number of contacts 1

Cross-section flexible conductor 1 - 6 mm<sup>2</sup>

Cross-section rigid conductor 1 - 4 mm<sup>2</sup>

**Use conditions**

Operating temperature -10 - +45 °C

**Dimensions**

Height 72 mm

Width 72 mm

Depth 48.50 mm

**Texts**

Switch mode Change-over contact

Installation mode For surface mounting

**Endurance**

Electrical durability at nominal load in AC1 in operating cycles 50000

**Texts**

Type of connection With screw terminals

**Voltage**

Rated operational voltage Ue 196 - 253 V

**Power**

Power loss at full load 1 W

**Settings**

Programme cycles Programme cycle: 24 hours

**Sustainability**

RoHS conform Yes