



EH711



IP20



Daily time switch 1 channel, analog, 72x72 with power reserve

Technical Features

Equipment

Number of channels	1
--------------------	---

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Power consumption during operation	0.50 VA
230 V incandescent and halogen lamp	1000 W
Power incandescent lamp	1000 - 1000 W

Functions

Number of function channels	1
-----------------------------	---

Connection

Number of contacts	1
Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1 - 4 mm ²

Use conditions

Operating temperature	-10 - +45 °C
-----------------------	--------------

Dimensions

Height	72 mm
Width	72 mm
Depth	48.50 mm

Texts

Switch mode	Change-over contact
Installation mode	For surface mounting

Endurance

Electrical durability at nominal load in AC1 in operating cycles	50000
--	-------

Texts

Type of connection	With screw terminals
--------------------	----------------------

Voltage

Rated operational voltage U _e	196 - 253 V
--	-------------

Power

Power loss at full load	1 W
-------------------------	-----

Settings

Programme cycles	Programme cycle: 24 hours
------------------	---------------------------

Sustainability

RoHS conform	Yes
--------------	-----