



JK2B14F2

**250A TP&N BOARD 14 WAY Flush enclosure**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Breaking and opening capacity ldm	0 kA
-----------------------------------	------

**Equipment**

Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Fixed load chassis

**Capacity**

Number of modules	14
-------------------	----

**Dimensions**

Height	945 mm
Width	470 mm
Depth	5 mm

**Cover, door**

Number of cabinet doors	1
Door/cover is transparent	No

**Materials**

Material	Steel
RAL code	9002
Colour	Grey white

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP41
Locking type	Special tool Without lock

**Architecture**

Number of poles	42
-----------------	----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes