



VT09TP

9M 1Row DIN Surface Metal BOX, 7.5M Door

Technical Features

Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Equipment

Number of rails	1
Number of rows	1

Capacity

Number of modules	9
-------------------	---

Dimensions

Height	250 mm
Width	259 mm
Depth	71 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	70 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	9
-----------------------	---

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	16
--------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
RAL code	9002
Colour	Grey white

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Snap on lock Without lock

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes