

Product Datasheet

VT09TP



VT09TP

9M 1Row DIN Surface Metal BOX, 7.5M Door

Technical Features

Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Surface mounting
-------------	------------------

Equipment

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

Capacity

Number of modules	9
-------------------	---

Dimensions

Height	250 mm
--------	--------

Width	259 mm
-------	--------

Depth	71 mm
-------	-------

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	70 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	9
-----------------------	---

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	16
--------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
----------	-------

RAL code	9002
----------	------

Colour	Grey white
--------	------------

Safety

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP30
-------------------------------	------

Locking type	Snap on lock Without lock
--------------	------------------------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----