



47468989

**SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,S1/B3/7**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Polar white

RAL code 9010

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

**Dimensions**

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth flush-mounted boxes 35 mm

Built-in depth 32 mm

**Connection**

Connector/plug type Plug-in terminal

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Plug-in connection

Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid Yes

With round protective earth pin No

With signal lamp No

With lock No

**Accessories**

Has labelling field Yes

**Cover, door**

Type of lid Self-closing hinged cover

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection Yes

Impact resistance IK IK05

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting No

---

**Texts**

Imprint	With imprint
Cover	Central cover plate
Type of connection	With plug-in terminals
Labelling	With labelling field

---

**Suitable for**

S.x/B.x

---

**Sustainability**

Halogen free	Yes
RoHS conform	Yes