



REQ024X



IK07

IP54



Door station AUDIO 24/2 2-wire stainless steel matt one

Technical Features

Materials

| | |
|----------------|-----------------|
| Surface finish | Matt |
| Material | Stainless steel |

Controls and indicators

| | |
|------------------------|----|
| Number of call buttons | 24 |
|------------------------|----|

Voltage

| | |
|-------------------|-----------|
| Operating voltage | 24 - 24 V |
|-------------------|-----------|

Dimensions

| | |
|------------|-----------------|
| Dimensions | 422 x 225.50 mm |
| Height | 422 mm |
| Width | 225.50 mm |
| Depth | 25 mm |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -20 - 55 °C |
| Storage/transport temperature | -30 - 80 °C |

Functions

| | |
|-------------------------|-------|
| Door communication type | Audio |
|-------------------------|-------|

Connection

| | |
|-------------------------|-----------------------|
| Conductor cross-section | 0 - 0 mm ² |
|-------------------------|-----------------------|

Installation, mounting

| | |
|-------------|------------------------------------|
| Mounting on | Flush mounting Surface mounting |
|-------------|------------------------------------|

Texts

| | |
|-------------------|--|
| Installation mode | For vertical mounting Break-proof flush-mounted call buttons Installation in surface-mounted or flush-mounted housings |
| Junction | Pluggable connection terminal block with screw terminals |
| Lighting | Durable, homogeneous, white LED call push-button backlighting |
| Protection | Loudspeaker and microphone protected against sabotage |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|