



SVN127

**Red LED Triple indicator light 230VAC**

**Technical Features**

**Capacity**

Number of modules

1

**Frequency**

Frequency

50 - 60 Hz

**Voltage**

Rated insulation voltage  $U_i$

400 V

Rated impulse withstand voltage  $U_{imp}$

4000 V

Rated operational voltage  $U_e$

230 - 230 V

Type voltage supply

AC

**Use conditions**

Operating temperature

-20 - 50 °C

Storage/transport temperature

-40 - 80 °C

**Connectivity**

Type of connection

Screw terminal

**Connection**

Cross-section flexible conductor

0.75 - 6 mm<sup>2</sup>

Cross-section rigid conductor

0.75 - 10 mm<sup>2</sup>

**Power**

Total power loss under IN

0.80 W

**Dimensions**

Height

83 mm

Width

17.50 mm

Depth

62 mm

**Lighting**

Type of lamp

LED

**Connection**

Type of lamp socket

Fix

**Materials**

Colour

Red

**Safety**

Ingress Protection (IP) class

IP20

**Power**

Power per charging point

0 kW

**Sustainability**

REACH-SVHC free

Yes