



BF441N

### Earth leakage add-on block 4P 40A 300mA AC Class

#### Technical Features

##### Architecture

Neutral position	Right
Number of poles	4

##### Capacity

Number of modules	3
-------------------	---

##### Voltage

Rated operational voltage $U_e$	230 - 400 V
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	4000 V

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Electric current

Rated residual operating current $I_{dn}$	300 mA
Rated current	40 A

##### Connectivity

Down connection alignment for modular devices	Aligned terminal
---	------------------

##### Installation, mounting

Nominal tightening torque	2.90 - 2.90 Nm
Nominal tightening torque down terminal	2.90 - 2.90 Nm

##### Dimensions

Height	70 mm
Width	35 mm
Depth	92 mm