



303501

Series switch, round supporting ring, light control

Technical Features

Electric current

Switching current 10 AX (100W LED (SBL))

Installation, mounting

Mounting on Flush mounting

Materials

Surface finish Matt

Material Metal
Plastic

Identification

Assembly arrangement Basic element

Connectivity

Mounting type Clamp mounting
Screw connection

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 71 x 71 mm

Built-in depth 31 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Impact resistance IK IK07

Architecture

Control/operation element Double rocker

Electric current

Rated current 10 A

Texts

Switch mode Series

Sustainability

Halogen free Yes

RoHS conform Yes