

Product Datasheet

WGDL131NP-12V

12V 3G press switch with led

Technical Features

Electric current	
Switching current	10 A
Voltage	
Rated voltage	250 V
Architecture	
Control/operation element	Double rocker
Materials	
Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Transparent	No
Dimensions	
Height	90 mm
Width	90 mm
Depth	25 mm
Controls and indicators	
Number of buttons	3
Connectivity	
Type of connection	Screw terminal
Safety	
Ingress Protection (IP) class	IP20
Texts	
Switch mode	1-way
Suitable for	
shark	
Sustainability	
RoHS conform	Yes