

**12V 3G press switch with led**

**Technical Features**

**Electric current**

Switching current	10 A
-------------------	------

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Control/operation element	Double rocker
---------------------------	---------------

**Materials**

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Transparent	No

**Dimensions**

Height	90 mm
Width	90 mm
Depth	25 mm

**Controls and indicators**

Number of buttons	3
-------------------	---

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Texts**

Switch mode	1-way
-------------	-------

**Suitable for**

shark	
-------	--

**Sustainability**

RoHS conform	Yes
--------------	-----