



VF412PF

Small distributor,golf,flush,4row,IP40,48M,MS-terminal,PE,white door

Technical Features

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

Installation, mounting

| | |
|----------------------------|----------------|
| Suitable for outdoor usage | No |
| Mounting on | Flush mounting |

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Equipment

| | |
|----------------------------|----|
| Number of rails | 4 |
| Number of rows | 4 |
| Number of section in width | 1 |
| With lock | No |
| Has neutral terminal block | No |

Capacity

| | |
|-------------------|----|
| Number of modules | 48 |
|-------------------|----|

Functions

| | |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

Dimensions

| | |
|-----------------|----------|
| Height | 688 mm |
| Width | 352 mm |
| Depth | 97.50 mm |
| Built-in height | 652 mm |
| Built-in width | 318 mm |

Cover, door

| | |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

Dimensions

| | |
|----------------|-------|
| Built-in depth | 72 mm |
|----------------|-------|

Cover, door

| | |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

Dimensions

| | |
|-----------------------|----|
| Number of width units | 12 |
|-----------------------|----|

Cover, door

| | |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

Materials

| | |
|----------|------------|
| Material | Plastic |
| RAL code | 9010 |
| Colour | Pure white |

Equipment

| | |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate | No |

Materials

| | |
|-----------------------|----|
| Ultraviolet-resistant | No |
|-----------------------|----|

Safety

| | |
|-------------------------------|--------------------|
| Protection class | Isolation class II |
| Impact resistance IK | IK07 |
| Ingress Protection (IP) class | IP40 |

Safety

| | |
|----------------|------------------------------|
| Locking type | Snap on lock Without lock |
| Glow wire test | 650 °C |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|