



WXF610

**Emergency stop switch gallery with key**

**Technical Features**

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

RAL code	7011
Surface finish	Matt
Material	Metal Plastic
Treatment	Untreated

**Identification**

Assembly arrangement	Middle plate
----------------------	--------------

**Connectivity**

Mounting type	Click mounting
---------------	----------------

**Controls and indicators**

Number of buttons	0
-------------------	---

**Dimensions**

Dimensions	45 x 45 mm
Built-in depth	40 mm
Built-in depth flush-mounted boxes	40 mm

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

**Architecture**

Control/operation element	Key
---------------------------	-----

**Electric current**

Rated current	10 A
---------------	------

**Texts**

Lighting	Without lighting (cannot be illuminated)
Switch mode	1-pole off

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes