



WXF641

**SUB-D15 (VGA+minijack) gallery screw ter**

**Technical Features**

**Connection**

|                       |     |
|-----------------------|-----|
| Connector/plug type   | VGA |
| Number of connections | 2   |

**Materials**

|                |                    |
|----------------|--------------------|
| Colour         | Grey               |
| RAL code       | 7011               |
| Surface finish | Matt               |
| Material       | Polycarbonate (PC) |
| Treatment      | Untreated          |

**Dimensions**

|                                    |          |
|------------------------------------|----------|
| Height                             | 45 mm    |
| Width                              | 45 mm    |
| Depth                              | 34.70 mm |
| Built-in depth flush-mounted boxes | 35 mm    |

**Connectivity**

|               |                                   |
|---------------|-----------------------------------|
| Mounting type | Claw mounting<br>Screw connection |
|---------------|-----------------------------------|

**Equipment**

|                 |    |
|-----------------|----|
| Shielded        | No |
| With dust cover | No |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK          | IK02 |

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10 - 35 °C |
|-----------------------|-------------|

**Texts**

|                                  |                         |
|----------------------------------|-------------------------|
| Outlet                           | With straight outlet    |
| Labelling                        | Without labelling       |
| Shielding                        | Housing unshielded      |
| Supporting plate/supporting ring | Without supporting ring |

**Suitable for**

|         |  |
|---------|--|
| gallery |  |
|---------|--|

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |