

# Product Datasheet

## 80164780



80164780



IP20



Push-button 4g, lab. field,RGB LED, int. temp.sensor, KNX-S.1/B.3/B.7,f.wh.p.wh.

### Technical Features

#### Installation, mounting

Mounting on Flush mounting

#### Use conditions

Operating temperature -5 - 45 °C

#### Electric current

Bus current consumption data transfer 20 mA

#### Functions

With room temperature controller No

#### Dimensions

Height 55.30 mm

Width 55.80 mm

Depth 13.85 mm

#### Equipment

Number of actuation points 8

#### Controls and indicators

With LED indication Yes

#### Materials

Colour White

RAL code 1013

Material Thermoplastic

Surface finish Glossy

#### Accessories

Has labelling field Yes

#### Screen

With display No

#### Texts

Function Function for manual interruption of automatic functions already triggered

Protection With dismantling protection

Temperature Integrated temperature sensor with output of the measured values via object

#### Sustainability

REACH-SVHC free Yes

RoHS conform Yes