



WXF644

**USB 3.0 socket gallery passthrough**

**Technical Features**

**Connection**

Connector/plug type	USB
Number of connections	0

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated

**Dimensions**

Height	40 mm
Width	45 mm
Built-in depth flush-mounted boxes	35 mm

**Connectivity**

Mounting type	Claw mounting Screw connection
---------------	-----------------------------------

**Equipment**

Shielded	No
With dust cover	No

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

**Use conditions**

Operating temperature	-10 - 35 °C
-----------------------	-------------

**Texts**

Outlet	With straight outlet
Labelling	Without labelling field
Shielding	Housing unshielded
Supporting plate/supporting ring	Without supporting ring

**Suitable for**

gallery	
---------	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes