



TYB692F



Output module 2x 6A /230V~, 2 inputs, flush mounted, KNX

Technical Features

Settings

Supported configuration mode ETS

Connectivity

With bus system KNX Yes

With bus system KNX radio No

Dimensions

Dimensions 44 x 43 mm

Height 44 mm

Width 43 mm

Depth 22 mm

Built-in depth 40 mm

Electric current

Rated current 6 A

Materials

Colour Light grey

Equipment

Radio frequency bidirectional No

With switch for manual switch Yes

Electric current

Bus current consumption while idle 5 mA

Frequency

Frequency 50 - 60 Hz

Power

Output power 500 W

230 V incandescent and halogen lamp 500 W

Voltage

Rated operational voltage U_e 230 - 230 V

System supply voltage 30 V DC Via bus

Operating voltage over bus 21 - 32 V

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature -5 - 45 °C

Connection

Cross-section rigid conductor 0.75 - 2.5 mm²

Cross-section flexible conductor 0.75 - 2.5 mm²

Texts

Function With safety functions e.g. for wind, rain, alarm
Binary input functions: Switching, dimming, blind, value transmitter,
scene, priority, timer operation, subplate
With positioning function for blind and lamella position
With sun shade function

Type of connection With screw terminals

Sustainability

RoHS conform Yes