



HWX041H

Auxiliary Switch low-level HW1 (AX)

Technical Features

Electric current

Rated current 230 V AC15 2 A

Connectivity

Mounting type Click mounting

Connection

Type of contacts 1x changeover

Voltage

Rated insulation voltage U_i 690 V

Rated impulse withstand voltage U_{imp} 1500 V

Type voltage supply AC/DC

Frequency

Frequency 50 - 60 Hz

Endurance

Number of mechanical operations 15000

Use conditions

Operating temperature -25 - 70 °C

Endurance

Electric endurance in number of cycles 3025

Use conditions

Storage/transport temperature -40 - 70 °C

Power

Total power loss under IN 0 W

Safety

Ingress Protection (IP) class IP4X

Sustainability

REACH-SVHC free Yes

RoHS conform Yes