



WRDP50NPSB

50A Double Pole Switch 1 Gang with LED Indicator Polished Steel Black Insert

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Silver
Surface finish	Glossy
Material	Stainless steel

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	86 x 86 mm
Built-in depth	20.20 mm

Electric current

Rated current	50 A
---------------	------

Texts

Lighting	With control LED for ON
Push button	No
Imprint	With clear terminal markings

Sustainability

RoHS conform	Yes
--------------	-----