



303701

Intermediate switch, round supporting ring, light control

Technical Features

Electric current	
Switching current	10 AX (100W LED (SBL))

Installation, mounting	
Mounting on	Flush mounting

Materials	
Surface finish	Matt
Material	Metal Plastic

Identification	
Assembly arrangement	Basic element

Connectivity	
Mounting type	Screw mounting Claw mounting

Controls and indicators	
Number of buttons	1

Dimensions	
Dimensions	76 x 76 mm
Built-in depth	32 mm
Built-in depth flush-mounted boxes	35 mm

Safety	
Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Architecture	
Control/operation element	Single rocker

Electric current	
Rated current	10 A

Texts	
Switch mode	Intermediate

Sustainability	
RoHS conform	Yes