

Product Datasheet

WXF315



WXF315

Electronic thermostat gallery

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Electric current

Rated current	8 A
Max. switching current	8 A

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Power supply

Supply voltage	230 V
----------------	-------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Settings

Comfort temperature setpoint	5 - 30 °C
------------------------------	-----------

Materials

Colour	White
RAL code	7011
Material	Polycarbonate (PC)
Treatment	Untreated

Dimensions

Height	45 mm
Width	45 mm
Depth	30 mm

Screen

With display	No
--------------	----

Equipment

Switching temperature difference	0.70 K
Type of thermostat	Digital
With heater	Yes

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Type of contacts	1NO
------------------	-----

Use conditions

Energy efficiency class	IV (2%)
-------------------------	---------

Texts

Thermal re-circulation	Without thermal return
------------------------	------------------------