



HWX047H

Fault trip Switch for HW1 (FS)

Technical Features

Electric current

Rated current 230 V AC15	4 A
--------------------------	-----

Connectivity

Mounting type	Click mounting
---------------	----------------

Connection

Type of contacts	1x changeover
------------------	---------------

Voltage

Rated insulation voltage U_i	690 V
Rated impulse withstand voltage U_{imp}	1500 V
Type voltage supply	AC/DC

Frequency

Frequency	50 - 60 Hz
-----------	------------

Endurance

Number of mechanical operations	15000
---------------------------------	-------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Endurance

Electric endurance in number of cycles	3025
----------------------------------------	------

Use conditions

Storage/transport temperature	-40 - 70 °C
-------------------------------	-------------

Power

Total power loss under IN	0 W
---------------------------	-----

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes